

510 CARTRIDGE SERIES • OEM ARTWORK

GLASS

ARTWORK GUIDE

This packet prepares branded artwork for the PROXY Glass 510 cartridge. Page 2 is the original factory dieline at 1:1 and carries both the 0.5 mL and 1.0 mL drawings. Work against the marked wrap bands, keep the threads and intake clear, and return a production-ready file with your editable source.

Artwork wraps a cylindrical body, so extend background art to the full wrap width and keep logos and type clear of the seam where the wrap closes.



1.0 mL
OPAQUE BLACK

0.5 mL
OPAQUE WHITE

PRINTABLE AREA

Device	GLASS • 10.5 mm dia • 61.7 mm (1.0 mL)
Surfaces	Wrap print around the glass body – marked on Page 2
1.0 mL wrap bands	33.30 mm wrap width • 1.0 mL: 26 mm band + 5 mm band
0.5 mL wrap bands	33.30 mm wrap width • 0.5 mL: 17 mm band + 5 mm band
Keep clear	Threads • intake hole • centre post • mouthpiece • metal base band
Body & finish	Glass body • 510 thread • open top fill • 1.4 • 2.0 mm intake

Dimensions are taken from the factory-supplied 1:1 drawing. The drawn boundaries on Page 2 are authoritative.

ARTWORK SETUP

Scale	Work at 1:1 against the Page 2 dieline • 0.5 mL and 1.0 mL are drawn separately
Accepted formats	PDF • SVG • PNG • JPG
Artwork files	Vector preferred • raster below ~150 ppi at placed size is flagged for review
Brand colors	List Pantone (PMS) references where defined and include them with your files
The dieline	Reference only – place artwork against it, never redraw or rescale it
Mouthpiece	Ceramic 10.5 × 26.55 mm • Plastic Round 10.65 × 17 mm • Plastic Flat 10.5 × 25.53 mm

On-screen color is an approximation. Production color is matched to the confirmed Pantone reference.


FILE DELIVERY

1 • Production file	Final wrap artwork at 1:1 on the Page 2 bands – PDF or SVG preferred
2 • Editable source	Original working file, kept editable – changes never mean redrawing
Submission	Via your PROXY representative
Printing	Wrap print around the glass body

BEFORE YOU SUBMIT

- ✓ Artwork sits inside the marked wrap bands on Page 2
- ✓ Threads, intake hole and mouthpiece kept clear
- ✓ Correct configuration selected • 0.5 mL or 1.0 mL • Snap Fit or Screw Fit
- ✓ Prepared at 1:1 • factory dieline unaltered
- ✓ Pantone references listed for any PMS-defined brand colors

1.0ml



0.5ml

